

Enabling Pressto-Test will block

access during

the exam to pre-

existing programs,

applications, data

Screens may vary slightly

by model and Operating

documents, files,

and pictures.

System (OS).

TI-Nspire[™] handhelds Test preparation: Press-to-Test

Use this method when exams require calculator clearing but allow documents and programs to be disabled, ratherthan deleted. This method also allows the option of disabling selected built-in functionality. Documents and + + programs can be recovered after the exam.

Before the exam – Put the calculator in Press-to-Test mode:

- 1) Ensure the handheld is turned off. Press @ [off] keys.
- Press and hold down esc and and mean keys simultaneously until Press-to-Test screen is displayed.



 Select restrictions: By default, all restrictions are selected. To change default restrictions, use arrow keys or
 key to scroll through list of restrictions. When a restriction is highlighted, press 🔄 to deselect the restriction. (Do not press the enter key.) To deselect all restrictions press etr. A keys.

- Enable Press-to-Test by pressing to select Enter Press-to-Test then pressing enter.
- **5)** The handheld will reboot and confirm restrictions. Select **OK** to continue to home screen.



6) When Press-to-Test is enabled, a lock icon will display in the upper right corner of the home screen.

ff	🔒 🕼
📨 Scratchpad	Documents
A Calculate	 New Document
B Graph	 My Documents
	3 Recent ▶
	Current
	5 Settings
×÷ +-	

An LED near the handheld's mini USB port will:

- » Flash green to indicate all restrictions (default) are selected
- » Flash amber to indicate one or more restrictions were disabled

If the handheld is in Press-to-Test mode and is to be used in subsequent exams, you can reset Pressto-Test to clear all data and files created during the previous exam.

If the calculator will not be used in subsequent exams, exiting Press-to-Test restores system settings and files that were restricted and clears all data and files created while in Press-to-Test mode.

After each exam – Reset Press-to-Test mode:

- 1) Ensure the handheld is turned off Press [m] [off] keys.
- 2) Press and hold down esc and and keys simultaneously until Press-to-Test screen is displayed.
- 3) Select Reset Press-to-Test and then OK.

After the exam – Exit Press-to-Test mode:

- Connect the handheld to another TI-Nspire[™] handheld using the USB unit-to-unit cable.
- 2) Press am for HOME screen. Press 2 to select My Documents





- This handheld is in Press-to-Test mode. Restrictions include: Angle Settings: Degree Pre-existing Scratchpad data, documents and folders are disabled. Limit geometry functions Disable function and conic grab and Market Press-to-Test
- 4) Select 1: Exit Press-to-Test Press ENTER.

∢ 1.1 ▶	Unsaved 🗢	A 🕼 🗙
г —	Documents	
	1: File 🕨	
	2: Edit	
	3: View 🕨	
	4: Insert 🕨 🕨	
	5: Page Layout 🕨 🕨	
	6: Refresh Libraries	
	7: 91. Exit Press-to-T	est
	8: L2: Transfer Press-	to-Test.
	🔒 9: F3: Help	

The handheld will reboot out of Press-to-Test mode

